
E33298

Process adapter for SMS pipe fitting

ADAPT IFM-SMS DN50/2" O-RG





EC 1935/2004 FDA

| Application | | |
|---|-------|--|
| Pressure rating | [bar] | 25 |
| Tests / approvals | | |
| Pressure Equipment Directive | | A possible classification to PED depends on the application and has to be carried out by the user / operator. |
| Pressure Equipment Directive EAC | | The adapter is intended for use in devices, machines and installations that do not fall under the categories of the technical rule TR CU 032/2013. |
| Safety instructions | | The compatibility between medium and product material has to be checked in all applications. |
| Mechanical data | | |
| Weight | [g] | 264.6 |
| Materials | | stainless steel (1.4435 / 316L) |
| Sensor connection | | G 1 internal thread Aseptoflex Vario |
| Process connection | | SMS pipe fitting DN50 (2") |
| Surface characteristics Ra/Rz of the wetted parts | | 0.4 / 4 |
| Sealing | | Gasket |
| Hygienic equipment class to DIN 11866 | | H4 |
| Accessories | | |
| Items supplied | | O-ring: 1 x 24 x 2, EPDM, FDA compliant, E30054 |

E33298

Process adapter for SMS pipe fitting





| Accessories (optional) | O-ring: 1 x 24 x 2, FKM, FDA compliant, E30123 |
|------------------------|--|
| | sealing ring: 1, PEEK, FDA compliant, E30124 |
| Remarks | |
| Pack quantity | 1 pcs. |